

ECOTENDING SINGLE OR - POWERED BY D:PLOY



TECH SPECIFICATIONS

- **MAX WORKPIECE WEIGHT**
11 kg
- **WORKPIECE DIMENSIONS**
For turned parts:
5-83 mm diameter and <250 mm length.
For milled parts: max 70x70 mm and <250 mm length.
Other dimensions are available as an optional by changing the grid
- **NUMBER OF WORKPIECES CAPACITY**
65 workpieces (other capacity is available as an option)
- **COMMUNICATION TO THE CNC MACHINE**
Digital I/O, Modbus TCP or Ethernet IP
- **SINGLE OR DUAL GRIPPER** Single
- **SOLUTION FOOTPRINT**
1.04 x 1.32 m
- **ROBOT MODEL**
UR10e

DIFFERENTIATION ELEMENTS ON THE BASE SOLUTION

- **BASE MATERIAL**
Alu. profile with covers
- **TYPE OF GRID FOR WORKPIECES**
Water drop shaped grid (other shapes are available as an option)
- **OPERATOR INTERFACE INCLUDED**
Not included
- **LIGHT INDICATORS**
Not included
- **MANUAL CONTROL BUTTONS**
Yes , for starting the application
- **CLEANING BLOWER INCLUDED**
Available as an option
- **CNC DOOR OPENER**
Yes included

SAFETY

- **SAFETY CERTIFICATION**
CE Included
- **SAFETY CONFIGURATION**
Integrated safety glass