

# MOVECOMPONENTS® CNC 12 SINGLE - POWERED BY D:PLOY



## TECH SPECIFICATIONS

- **MAX WORKPIECE WEIGHT**  
10 kg
- **WORKPIECE DIMENSIONS**  
For turned parts:  
max 100 mm diameter.  
For milled parts:  
max 70x70 mm  
Other dimensions are available as an optional by changing the grid
- **NUMBER OF WORKPIECES CAPACITY**  
64 workpieces (other capacity is available as an option)
- **COMMUNICATION TO THE CNC MACHINE**  
Digital I/O, Modbus TCP or Ethernet IP
- **SINGLE OR DUAL GRIPPER** Single
- **SOLUTION FOOTPRINT**  
1.5 x 1.5 m
- **ROBOT MODEL**  
JAKA Zu12

## DIFFERENTIATION ELEMENTS ON THE BASE SOLUTION

- **BASE MATERIAL**  
Bent sheet metal
- **TYPE OF GRID FOR WORKPIECES**  
Squared shaped (other shapes are available as an option)
- **OPERATOR INTERFACE INCLUDED** Yes (tablet)
- **LIGHT INDICATORS**  
Not included
- **MANUAL CONTROL BUTTONS**  
Not included
- **CLEANING BLOWER INCLUDED**  
Available as an option
- **CNC DOOR OPENER**  
Yes, single door included (double door available as an option)

## SAFETY

- **SAFETY CERTIFICATION**  
CE Included
- **SAFETY CONFIGURATION**  
Integrated safety scanner