

APALLET

- powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
 - **FOOTPRINT**
2.6 m x 1.5 m
 - **MAX BOX PAYLOAD***
15 kg (Up to 27 kg coming soon!)
 - **MAX PALLET HEIGHT***
2.1 m
 - **FLEXIBLE PALLET SIZES**
Yes
 - **ROBOT MODEL**
Fanuc CRX-30iA
 - **ROBOT MOUNTING**
Fixed pedestal
- * Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
Not included
- **SAFETY CONFIGURATION**
Cobot mode (as an option, external safety elements can be included to increase cycle time)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Alu. profile with metal covers
- **PALLET DETECTION**
Photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, robot tablet
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
Not included
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price