

COPA-F 2000

- powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
1.4 m x 1 m
- **MAX BOX PAYLOAD***
15 kg
- **MAX PALLET HEIGHT***
1.6 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
Fanuc CRX-30iA
- **ROBOT MOUNTING**
Fixed pedestal

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
Not included
- **SAFETY CONFIGURATION** Cobot mode (as an option, safety scanners can be included to increase cycle time)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Metal powder coated
- **PALLET DETECTION**
Two photoelectric sensors
- **OPERATOR INTERFACE INCLUDED**
Yes, robot tablet
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
No in
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price