

FCP 12,5 OR LIFT

- powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
3 m x 1.6 m
- **MAX BOX PAYLOAD***
9 kg
- **MAX PALLET HEIGHT***
2.1 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
UR10e
- **ROBOT MOUNTING**
OnRobot Lift100

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION****
CE available as an option
- **SAFETY CONFIGURATION**
Cobot mode (as an option, a U-shape fence with scanner can be included to increase cycle time)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Bent sheet metal
- **PALLET DETECTION**
Photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Not included
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
No available
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price