


CO-BOX (20)

- powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
2.3 m x 1.5 m
- **MAX BOX PAYLOAD**
15 kg
- **MAX PALLET HEIGHT***
1.8 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
UR20
- **ROBOT MOUNTING**
Fixed pedestal

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
CE is included
- **SAFETY CONFIGURATION** Cobot mode (as an option, a U-shape fence with scanner can be included to increase cycle time)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Alu. profile
- **PALLET DETECTION**
OnRobot pallet station
- **OPERATOR INTERFACE INCLUDED**
Not included
- **LIGHT INDICATORS**
Yes, pallet presence indicator
- **MANUAL CONTROL BUTTONS**
Not included
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER**
Not included

** The inclusion of additional features may affect the final price