

QP20

- POWERED BY D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
3 box/min collaborative mode
10 box/min high-speed mode
- **FOOTPRINT**
3 m x 1.3 m
- **MAX BOX PAYLOAD**
15 kg
- **MAX PALLET HEIGHT***
2 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
Fanuc CRX-20iA/L
- **ROBOT MOUNTING**
OnRobot Lift100

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
CE is included
- **SAFETY CONFIGURATION**
Cobot mode (as an option, 3 safety scanners can be included to increase cycle time)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Alu. Profile
- **PALLET DETECTION**
OnRobot pallet station
- **OPERATOR INTERFACE INCLUDED**
Yes, robot tablet
- **LIGHT INDICATORS**
Yes, application status indicator and pallet presence indicator
- **MANUAL CONTROL BUTTONS**
Not included
- **CONVEYOR****
Available as an option
- **INERLAYER CONTAINER**
Not included

** The inclusion of additional features may affect the final price