

STACKSMART1212

- powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
3 m x 1.3 m
- **MAX BOX PAYLOAD***
10 kg
- **MAX PALLET HEIGHT***
2.2 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
TM12S-X
- **ROBOT MOUNTING**
OnRobot Lift100

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
UKCA is included
- **SAFETY CONFIGURATION**
A U-shape fence with 1 safety scanner is included

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Single side (Dual side available as an option)
- **BASE MATERIAL**
Alu. Profile with covers
- **PALLET DETECTION**
Photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, touchscreen HMI
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
Yes, start/stop button
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price