



4 x Ø 5 [0.197] THRU ALL
 M6 - 6H THRU ALL
 ✓ Ø 6.05 [0.238] X 90°, Near Side
 ✓ Ø 6.05 [0.238] X 90°, Far Side

4 x Ø 6.60 [0.260] THRU ALL
 □ Ø 10.40 [0.409] ▽ 4.30 [0.169]

