

MOVECOMPONENTS® CNC 12 DUAL - POWERED BY D:PLOY



TECH SPECIFICATIONS

- **MAX WORKPIECE WEIGHT**
4.5 kg
- **WORKPIECE DIMENSIONS**
For turned parts:
max 100 mm diameter.
For milled parts:
max 70x70 mm
Other dimensions are available as an optional by changing the grid
- **NUMBER OF WORKPIECES CAPACITY**
64 workpieces (other capacity is available as an option)
- **COMMUNICATION TO THE CNC MACHINE**
Digital I/O, Modbus TCP or Ethernet IP
- **SINGLE OR DUAL GRIPPER**
Dual gripper
- **SOLUTION FOOTPRINT**
1.5 x 1.5 m
- **ROBOT MODEL**
JAKA Zu12

SAFETY

- **SAFETY CERTIFICATION**
CE Included

DIFFERENTIATION ELEMENTS ON THE BASE SOLUTION

- **BASE MATERIAL**
Bent sheet metal
- **TYPE OF GRID FOR WORKPIECES**
Squared shaped (other shapes are available as an option)
- **OPERATOR INTERFACE INCLUDED**
Yes, tablet
- **LIGHT INDICATORS**
Not included
- **MANUAL CONTROL BUTTONS**
Not included
- **CLEANING BLOWER INCLUDED**
Available as an option
- **CNC DOOR OPENER**
Yes, single door included (double door available as an option)

- **SAFETY CONFIGURATION**
Integrated safety scanner