

# S:PAL

- powered by D:PLOY



## TECH SPECIFICATIONS

- **MAX CYCLE TIME\***  
10 box/min
- **FOOTPRINT**  
1.5 m x 1.8 m
- **MAX BOX PAYLOAD\***  
15 kg (Up to 27 kg coming soon!)
- **MAX PALLET HEIGHT\***  
2 m
- **FLEXIBLE PALLET SIZES**  
Yes
- **ROBOT MODEL**  
Fanuc CRX-30iA
- **ROBOT MOUNTING**  
Fixed pedestal

\* Actual performance may differ depending on setup and other environmental factors

## SAFETY

- **SAFETY CERTIFICATION**  
CE is included
- **SAFETY CONFIGURATION**  
Cobot mode (as an option, external safety elements can be included to increase cycle time)

## UNIQUE FEATURES

- **PALLET ARRANGEMENT**  
Single side
- **BASE MATERIAL**  
Alu. Profile with covers
- **PALLET DETECTION**  
Two photoelectric sensors
- **OPERATOR INTERFACE INCLUDED**  
Yes, robot tablet
- **LIGHT INDICATORS**  
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**  
Yes (manual pallet confirmation button)
- **CONVEYOR\*\***  
Available as an option
- **INTERLAYER CONTAINER\*\***  
Available as an option

\*\* The inclusion of additional features may affect the final price