

ROBPAL

- powered by D:PLOY

TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
2.45 x 1.3 m
- **MAX BOX PAYLOAD***
15 kg (Up to 22 kg coming soon!)
- **MAX PALLET HEIGHT***
2.1 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
UR20
- **ROBOT MOUNTING**
Fixed pedestal

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
Yes (CE)
- **SAFETY CONFIGURATION**
Cobot mode (as an option, external safety elements can be included to increase cycle time)



UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Bent sheet metal
- **PALLET DETECTION**
Photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, tablet
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
Not available
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price