



PROPAL20L

- powered by D:PLOY

TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
3 m x 1 m
- **MAX BOX PAYLOAD***
12 kg
- **MAX PALLET HEIGHT***
2.4 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
Jaka Zu20
- **ROBOT MOUNTING**
OnRobot Lift100

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
Not included
- **SAFETY CONFIGURATION** Cobot mode (as an option, safety scanners can be included to increase cycle time)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Stainless steel
- **PALLET DETECTION**
2 photoelectric sensors
- **OPERATOR INTERFACE INCLUDED**
Yes, tablet
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
Yes (start/stop button, program selection buttons)
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER ****
Available as an option

** The inclusion of additional features may affect the final price